

INFINITY PHOTO-OPTICAL TS-160 LENS ASSEMBLY GUIDE

Body



Macro Pro



- **135mm LENS**
- 4x MACRO
- PORTRAIT LENS

Micro HM



- **100mm LENS**
- 16x MICRO
- DEEP FOCUS
- INF to ~ 50cm (20in)

SFX-1



- **100mm LENS**
- DEEP FOCUS
- INF to ~ 50cm (20in)

SFX-2



- **50mm LENS**
- DEEP FOCUS
- INF to ~ 15cm (6in)

SFX-3



- **35mm LENS**
- DEEP FOCUS
- INF to ~ 5cm (2in)

- **T2 NEUTRAL MT**
- FOCUS RING
- IRIS CONTROL

SCREW LENS TO MAIN BODY

REFER TO ROADMAP INSTRUCTIONS FOR ADDITIONAL INFO

T2 PL Mount



Additional T2 Mounts

Sony
Canon
Nikon
Leica
Lumix
Olympus



INFINITY PHOTO-OPTICAL 45° and 90° PRISM ASSEMBLY GUIDE

Setup for 45° Prism and 90° Prism (Shown)

REFER TO ROADMAP INSTRUCTIONS FOR ADDITIONAL INFO

Micro HM



UNSCREW SPACER



SCREW ON PRISM



* Install 8mm Spacer

ASSEMBLED



SFX-1



* Install 5mm Spacer



SFX-2



* Install 5mm Spacer



SFX-3



* Install 8mm Spacer



Macro Pro



No Prisms Used

* Each Prism comes with 5mm and 8mm spacer

45° Prism



Assembled

90° Prism



Assembled

FlipR



Unlock Horizon Adjust
To Level Image

